

TORONTO

23 BERTRAND AVENUE
TORONTO, ONTARIO
CANADA, M1L 2P3
+1 416 755 2291

BUFFALO

93 EAST AVENUE
NORTH TONAWANDA, NEW YORK
U.S.A., 14120-6594
+1 716 693 8813

DROITWICH SPA

POINTON WAY,
STONEBRIDGE CROSS BUSINESS PARK
DROITWICH SPA, WORCESTERSHIRE
UNITED KINGDOM, WR9 0LW
+44 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN
MARGOSA ROAD, MALLESWARAM
BANGALORE, INDIA, 560 003
+91 80 4906 3555

SHANGHAI

UNIT 903, 888 NORTH SICHUAN RD.
HONGKOU DISTRICT, SHANGHAI
CHINA, 200085
+86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO,
1370 GALPÃO 6 EMBU DAS ARTES
SAO PAULO, BRAZIL
+55 11 4785 1330

LYON

93 RUE DE LA VILLETTE
LYON, 69003 FRANCE
+33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402
P.O.BOX 18226 JAFZA,
DUBAI - UNITED ARAB EMIRATES
+971 4 887 6775

MANNHEIM

DYNAMOSTRASSE 13
68165 MANNHEIM
GERMANY
+49 621 3999 9858

JIMBOLIA

STR CALEA MOTILOR NR. 2C
JIMBOLIA 305400, JUD.TIMIS
ROMANIA
+40 256 360 030

ARMSTRONG FLUID TECHNOLOGY
ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

VERTICAL IN-LINE | 50 HZ | SELECTION CHARTS

File No: F43.205
Date: OCTOBER 12, 2021
Supersedes: F43.205
Date: SEPTEMBER 23, 2021

PUMP	FLOW USgpm (L/s)	SPEED rpm	PRESSURE RANGE PSI (kPa)		
			UL	ULC	FM
2×1.5 LA-F	50 (3)	2945	—	—	40 (276) – 92 (634)
	75 (5)	2945	—	—	40 (276) – 91 (627)
2×2×8 FM 43PF	50 (3)	2945	43 (296) – 86 (593)	43 (296) – 86 (593)	44 (303) – 86 (593)
	75 (5)	2945	—	—	44 (303) – 86 (593)
	100 (60)	2945	41 (283) – 86 (593)	41 (283) – 86 (593)	43 (296) – 86 (593)
3×3×8 FM 43PF	200 (13)	2945	44 (303) – 83 (572)	44 (303) – 83 (572)	43 (296) – 83 (572)
	250 (16)	2945	42 (290) – 83 (572)	42 (290) – 83 (572)	42 (290) – 83 (572)
	300 (19)	2945	40 (276) – 82 (565)	40 (276) – 82 (565)	40 (276) – 82 (565)
4×3×9 PF	300 (19)	2970	56 (386) – 94 (648)	56 (386) – 94 (648)	56 (386) – 94 (648)
	400 (25)	2970	60 (414) – 91 (627)	60 (414) – 91 (627)	60 (414) – 91 (627)
	450 (28)	2970	—	—	83 (572) – 89 (614)
	500 (32)	2970	78 (538) – 86 (593)	78 (538) – 86 (593)	79 (545) – 86 (593)
6×4 LA-F	400(25)	2945	—	—	40 (276) – 91 (627)
8×8×15 FM	1000(63)	1480	49 (338) – 72 (496)	49 (338) – 72 (496)	49 (338) – 72 (496)
	1250(79)	1480	46 (317) – 70 (483)	46 (317) – 70 (483)	46 (317) – 70 (483)
8×8×16 FM	1000(63)	1480	56 (386) – 68 (469)	56 (386) – 68 (469)	56 (386) – 68 (469)
	1250(79)	1480	52 (359) – 64 (441)	52 (359) – 64 (441)	52 (359) – 64 (441)