


**EXHAUST SYSTEM | SUBMITTAL DRAWING**


File No: F43.456  
 Date: DEC. 12, 2014  
 Supersedes: F43.456  
 Date: AUG. 18, 2011

Job: \_\_\_\_\_ Representative: \_\_\_\_\_  
 \_\_\_\_\_ Order no.: \_\_\_\_\_ Date: \_\_\_\_\_  
 Engineer: \_\_\_\_\_ Submitted by: \_\_\_\_\_ Date: \_\_\_\_\_  
 Contractor: \_\_\_\_\_ Approved by: \_\_\_\_\_ Date: \_\_\_\_\_

**TYPE 1  
 NPT MALE**



**TYPE 2  
 ANSI 150# FLANGES**



**NOTE:**  
 If pipe length between engine exhaust and silencer is more than 15 feet, silencer may need to be larger than indicated sizes. Refer to factory.

2

## SILENCERS


ENGINE MANUFACTURER	TYPE	CONNECTION SIZE	ENGINE MODEL	A	B	C	D
Clarke	1	3" NPT	JU4H-UF10, 12, 14, 20, 22, 24	3.00 (76)	8.00 (203)	20.00 (508)	26.00 (660)
	2	4" flanged (150#)	JU4H-UF34, H0, H2, 40, 42, 50, 52, 54, 58, AD5G, ADPO, ADRO, ADW8, ADY8, AEAO, AEE8, AEF2, ADJ8, ADJ2, AD98	4.00 (102)	10.00 (254)	25.00 (635)	31.00 (787)
		5" flanged (150#)	JU6H-UF34, 54, AB76, 84, DO, D2, 30, 32, M8, MO, M2, 58, 50, 52, 60, 62, AAQ8, AARG, AD58, ADNG, ADN0, ADP8, AD88, ADMG, AAPG, AASO	5.00 (127)	12.00 (305)	30.00 (762)	38.00 (965)
			DP6H-UFAA50, AA62, AA88, AAX8				
		5" flanged (150#) quantity 2 per engine	DR8H-UFAA40, AA5G, AA68, AA62	6.00 (152)	14.00 (356)	35.00 (889)	43.00 (1092)
			DSOH-UFAANO, AA68, AA60, AAMO, AA98, AA92				
		6" flanged (150#)	JU6H-UFADPO, ADQO, ADR8, ADRO, ADS8, ADSO, ADW8, ADTO, ADX8, AD98	6.00 (152)	14.00 (356)	35.00 (889)	43.00 (1092)
	JW6H-UFAA60, AA80, ADFO, ADJO, AD70, AD80						
	DP6H-UFAA70						
	6" flanged (150#) quantity 2 per engine	DT2H-UFAA20, AA58, AA50, AA60, AA88, AA98, AA92	8.00 (203)	18.00 (457)	45.00 (1143)	53.00 (1346)	
8" flanged (150#)	JX6H-UFADFO, AD60, ADN0, ADPO, AD88	8.00 (203)	18.00 (457)	45.00 (1143)	53.00 (1346)		
Cummins	2	4" flanged (150#)	CFP5E-F10, F20, F30, F40, F50	4.00 (102)	10.00 (254)	25.00 (635)	31.00 (787)
			CFP59-F10, F20, F40, F50				
			CFP7E-F10, F20, F30, F40, F50, F60				
	5" flanged (150#)	CFP83-F10, F20, F30	5.00 (127)	12.00 (305)	30.00 (762)	38.00 (965)	
		CFP9E-F10, F20, F30, F40, F50, F60					
		CFP11E-F20					
	6" flanged (150#)	CFP15E-F10, F20, F30, F40	6.00 (152)	14.00 (356)	35.00 (889)	43.00 (1092)	
	8" flanged (150#)	CFP15E-F50, F60, F70	8.00 (203)	18.00 (457)	45.00 (1143)	53.00 (1346)	

## NOTES:

- 1 Dimensions are not to be used for construction purpose unless certified.
- 2 Data subject to change without notice.
- 3 All dimensions are in inches (mm).

**FLEXIBLE EXHAUST CONNECTORS**

ENGINE MANUFACTURER	TYPE	CONNECTION SIZE	ENGINE MODEL
Clarke	B	3" NPT	JU4H-UF10, 12, 14, 20, 22, 24, AEA0, AEE8, AEF2, ADJ8, ADJ2
		4" NPT	JU4H-UF34, H0, H2, 40, 42, 50, 52, 54, 58, AD5G, ADPO, ADRO, ADW8, ADY8, AD98
	C	5" flanged (150#)	JU6H-UF34, 54, AB76, 84, D0, D2, 30, 32, M8, M0, M2, 58, 50, 52, 60, 62, AAQ8, AARG, AD58, ADNG, ADNO, ADP8, AD88, ADMG, AAPG, AASO
			DP6H-UFAA50, AA62, AA88, AAX8
	H	5" flanged (150#) Quantity 2 per engine	DR8H-UFAA40, AA5G, AA68, AA62
			DSOH-UFAANO, AA68, AA60, AAMO, AA98, AA92
	C	6" flanged (150#)	JU6H-UFADPO, ADQ0, ADR8, ADRO, ADS8, ADSO, ADW8, ADTO, ADX8, AD98
			JW6H-UFAA60, AA80, ADF0, ADJO, AD70, AD80
			DP6H-UFAA70
	H		DQ6H-UFAA50, AA60, AA88, AA98
	H	6" flanged (150#) Quantity 2 per engine	DT2H-UFAA20, AA58, AA50
	A	8" flanged (150#)	JX6H-UFADFO, AD60, ADNO, ADPO, AD88
H	8" flanged (150#) Quantity 2 per engine	DT2H-UFAA60, AA88, AA98, AA92	
Cummins	A	4" NPT	CFP5E-F10, F20, F30, F40, F50
			CFP59-F10, F20, F40, F50
			CFP7E-F10, F20, F30, F40, F50, F60
			CFP83-F10, F20, F30
			CFP9E-F10, F20, F30, F40, F50, F60
		5" NPT	CFP11E-F20
	6" NPT	CFP15E-F10, F20, F30, F40, F50, F60, F70	



**TORONTO**

23 BERTRAND AVENUE  
TORONTO, ONTARIO  
CANADA  
M1L 2P3  
+1 416 755 2291

**BUFFALO**

93 EAST AVENUE  
NORTH TONAWANDA, NEW YORK  
U.S.A.  
14120-6594  
+1 716 693 8813

**BIRMINGHAM**

HEYWOOD WHARF, MUCKLOW HILL  
HALESOWEN, WEST MIDLANDS  
UNITED KINGDOM  
B62 8DJ  
+44 (0) 8444 145 145

**MANCHESTER**

WOLVERTON STREET  
MANCHESTER  
UNITED KINGDOM  
M11 2ET  
+44 (0) 8444 145 145

**BANGALORE**

#59, FIRST FLOOR, 3RD MAIN  
MARGOSA ROAD, MALLESWARAM  
BANGALORE, INDIA  
560 003  
+91 (0) 80 4906 3555

**SHANGHAI**

NO. 1619 HU HANG ROAD, XI DU TOWNSHIP  
FENG XIAN DISTRICT, SHANGHAI  
P.R.C.  
201401  
+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY  
ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

**MAKING  
ENERGY  
MAKE  
SENSE™**