

HORIZONTAL SPLIT CASE PUMP | SERIES 4600F |
DIESEL DRIVEN | 14x10x20F | SUBMITTAL

File No: F46-5681
Date: FEBRUARY 16, 2022
Supersedes: NEW
Date: NEW

Job: _____ Representative: _____
Order no.: _____ Date: _____
Engineer: _____ Submitted by: _____ Date: _____
Contractor: _____ Approved by: _____ Date: _____

PUMP DESIGN DATA

Flow: _____
Head: _____

ENGINE DESIGN DATA

HP: _____ RPM: _____
Bat. Voltage: _____ Tank size: _____
Other: _____

NOTES

- 1 Std. Discharge flange thickness ANSI 250#.
- 2 Coupling guard not shown.
- 3 All dimensions for engine connections are with reference to engine manufacturer's installation drawings.
- 4 Do not use for construction unless certified.
- 5 Right hand rotation only.

FLANGE RATING

- ANSI 125# STD¹
- ANSI 125# Suction
250# Discharge
- ANSI 250#
- PN 16

FIRE PUMP LISTING

- UL
- ULC
- FM

ACCESSORIES

- Exhaust system
- Fuel system
- Cooling system (mounted on engine)
- Battery system

14x10x20F	HORIZONTAL SPLIT CASE DIESEL DRIVEN	DIMENSIONS inches (mm)							WEIGHT
		C	HA	HB	HE	HF	HM	Z	lbs (kg)
Clarke	JU6H series	126.97 (3225)	37.40 (950)	129.92 (3300)	34.65 (880)	61.02 (1550)	81.93 (2081)	21.59 (548)	4157 (1886)
	JW6H series	126.91 (3224)	37.40 (950)	129.92 (3300)	34.65 (880)	61.02 (1550)	86.57 (2199)	21.59 (548)	4558 (2067)
	DP6H series	128.22 (3257)	37.40 (950)	129.92 (3300)	34.65 (880)	61.02 (1550)	82.50 (2095)	21.59 (548)	4714 (2138)
	DQ6H series	127.34 (3235)	38.58 (980)	129.92 (3300)	35.83 (910)	61.02 (1550)	84.49 (2146)	21.60 (549)	4964 (2252)
	DS0H series	130.18 (3307)	41.34 (1050)	133.86 (3400)	38.58 (980)	62.99 (1600)	81.99 (2083)	21.59 (548)	5664 (2569)
	C18H0 series	137.66 (3497)	37.40 (950)	137.80 (3500)	34.45 (875)	65.94 (1675)	82.11 (2086)	19.14 (486)	6564 (2977)
	DR8H series	111.42 (2830)	41.34 (1050)	125.98 (3200)	38.58 (980)	59.06 (1500)	79.62 (2022)	21.59 (548)	5164 (2342)
	DT2H series	135.26 (3436)	37.40 (950)	133.86 (3400)	34.45 (875)	62.99 (1600)	78.66 (1998)	19.14 (486)	6964 (3159)
Cummins	CFP9E series	141.09 (3584)	32.00 (813)	122.00 (3099)	30.00 (762)	39.00 (991)	77.37 (1965)	18.25 (464)	5934 (2692)
	CFP15E series	142.77 (3626)	40.00 (1016)	145.00 (3683)	38.00 (965)	47.00 (1194)	74.15 (1883)	18.25 (464)	7314 (3318)

TORONTO
+1 416 755 2291

BUFFALO
+1 716 693 8813

DROITWICH SPA
+44 8444 145 145

MANCHESTER
+44 8444 145 145

BANGALORE
+91 80 4906 3555

SHANGHAI
+86 21 5237 0909

SÃO PAULO
+55 11 4785 1330

LYON
+33 4 26 83 78 74

DUBAI
+971 4 887 6775

MANNHEIM
+49 621 3999 9858

JIMBOLIA
+40 256 360 030

