

HORIZONTAL SPLIT CASE PUMP | SERIES 4600F |
DIESEL DRIVEN | 12x8x18F | SUBMITTAL

File No: F46.566
Date: SEPTEMBER 25, 2018
Supersedes: F46.566
Date: AUGUST 10, 2016

Job: _____ Representative: _____
_____ Order no.: _____ Date: _____
Engineer: _____ Submitted by: _____ Date: _____
Contractor: _____ Approved by: _____ Date: _____

PUMP DESIGN DATA

Flow: _____
Head: _____

ENGINE DESIGN DATA

HP: _____ RPM: _____
Bat. Voltage: _____ Tank size: _____
Other: _____

NOTES

- 1 Std. Discharge flange thickness ANSI 250#.
- 2 Coupling guard not shown.
- 3 All dimensions for engine connections are with reference to engine manufacturer's installation drawings.
- 4 Do not use for construction unless certified.
- 5 Right hand rotation only.

FLANGE RATING

- ANSI 125# STD¹
- ANSI 125# Suction
250# Discharge
- ANSI 250#
- PN 16

FIRE PUMP LISTING

- UL
- ULC
- FM

ACCESSORIES

- Exhaust system
- Fuel system
- Cooling system (mounted on engine)
- Battery system

12x8x18F	HORIZONTAL SPLIT CASE DIESEL DRIVEN	DIMENSIONS inches (mm)							WEIGHT
		C	HA	HB	HE	HF	HM	Z	lbs (kg)
Clarke	JU6H series	105.48 (2679)	32.00 (813)	106.00 (2692)	30.00 (762)	51.00 (1295)	43.25 (1099)	16.50 (419)	4577 (2076.1)
	JW6H series	111.78 (2839)	32.00 (813)	110.00 (2794)	30.00 (762)	35.25 (895)	46.95 (1193)	16.50 (419)	4968 (2253.2)
	JX6H series	118.52 (3010)	32.00 (813)	118.00 (2997)	30.00 (762)	57.00 (1448)	47.25 (1200)	16.50 (419)	6281 (2849.1)
Cummins	CFP59 series	96.83 (2459)	32.00 (813)	98.00 (2489)	30.00 (762)	47.00 (1194)	52.69 (1338)	16.50 (419)	4249 (1927.5)
	CFP83 series	104.93 (2665)	32.00 (813)	102.00 (2591)	30.00 (762)	49.00 (1245)	54.27 (1378)	16.50 (419)	4643 (2106.1)
	CFP5E series	95.37 (2422)	32.00 (813)	98.00 (2489)	30.00 (762)	47.00 (1194)	52.78 (1341)	16.50 (419)	4113 (1865.6)
	CFP7E series	106.32 (2701)	32.00 (813)	106.00 (2692)	30.00 (762)	51.00 (1295)	52.78 (1341)	16.50 (419)	4323 (1960.8)
	CFP9E series	108.11 (2746)	32.00 (813)	106.00 (2692)	30.00 (762)	51.00 (1295)	54.88 (1394)	16.50 (419)	4748 (2153.7)
	CFP11E series	120.41 (3058)	40.00 (1016)	130.00 (3302)	38.00 (965)	63.00 (1600)	55.88 (1419)	16.50 (419)	5719 (2594.3)
	CFP15E series	132.12 (3356)	40.00 (1016)	130.00 (3302)	38.00 (965)	63.00 (1600)	46.72 (1187)	16.50 (419)	7525 (3413.4)

TORONTO
+1 416 755 2291

BUFFALO
+1 716 693 8813

BIRMINGHAM
+44 (0) 8444 145 145

MANCHESTER
+44 (0) 8444 145 145

BANGALORE
+91 (0) 80 4906 3555

SHANGHAI
+86 21 3756 6696

SÃO PAULO
+55 11 4785 1330

