


## ARMkool 8 Vertical Pipe-mounted w/Panel Rack Remote No Options

## SUBMITTAL

JOB: _____	REPRESENTATIVE: _____
_____	_____
_____	_____
ENGINEER: _____	ORDER NO: _____ DATE: _____
CONTRACTOR: _____	SUBMITTED BY: _____ DATE: _____
	APPROVED BY: _____ DATE: _____



### DIMENSIONS inches (mm)

	W	L	H (max)	A	B	C
ARMkool 8 FS R V520 Z520 NC S	92.63 (2353)	110.50 (2807)	85.75 (2178)	8.50 (216)	65.50 (1664)	79.00 (2007)
ARMkool 8 FS R V640 Z640 NC S	86.63 (2200)	93.38 (2372)	85.75 (2178)	6.75 (172)	61.25 (1556)	79.00 (2007)
ARMkool 8 FS R V750 Z750 NC S	92.63 (2353)	110.50 (2807)	85.75 (2178)	8.50 (216)	65.50 (1664)	79.00 (2007)
ARMkool 8 FS R V875 Z875 NC S	95.63 (2429)	111.75 (2839)	86.00 (2184)	8.50 (216)	68.50 (1740)	79.25 (2013)

### WEIGHT lbs. (kg)

	Fixed Speed	Variable Speed
Armcool 8 FS R V520 Z520 NC S	10834 (4925)	11584 (5265)
Armcool 8 FS R V640 Z640 NC S	10354 (4706)	10956 (4980)
Armcool 8 FS R V750 Z750 NC S	10966 (4985)	11716 (5325)
Armcool 8 FS R V875 Z875 NC S	13166 (5985)	14166 (6439)

Armstrong Pumps Inc.  
93 East Avenue  
North Tonawanda, New York  
U.S.A. 14120-6594  
Tel: (716) 693-8813  
Fax: (716) 693-8970

S.A. Armstrong Limited  
23 Bertrand Avenue  
Toronto, Ontario  
Canada, M1L 2P3  
Tel: (416) 755-2291  
Fax: (416) 759-9101



Armstrong Pumps Limited  
Peartree Road, Stanway  
Colchester, Essex  
United Kingdom, CO3 0LP  
Tel: 01206-579491  
Fax: 01206-760532

Armstrong Darling  
2200 Place Transcanadienne  
Montreal, Quebec  
Canada, H9P 2X5  
Tel: (514) 421-2424  
Fax: (514) 421-2436

Visit us at [www.armstrongpumps.com](http://www.armstrongpumps.com)

© S.A. Armstrong Limited 2002

