

END SUCTION ELECTRIC FIRE PUMP |

60 HZ | SELECTION CHARTS

File No: F40.200
 Date: AUGUST 10, 2016
 Supersedes: F40.225
 Date: MARCH 7, 2008

PUMP	FLOW USgpm (L/s)	SPEED rpm	PRESSURE RANGE PSI (kPa)		
			UL	ULC	FM
4×3×8.5 FM	250 (16)	3560	57 (393) - 135 (931)	57 (393) - 135 (931)	57 (393) - 136 (938)
	300 (19)	3560	55 (379) - 134 (936)	55 (379) - 134 (936)	55 (379) - 135 (931)
	400 (25)	3560	48 (331) - 131 (903)	48 (331) - 131 (903)	48 (331) - 132 (910)
	450 (28)	3560	76 (524) - 129 (889)	76 (524) - 129 (889)	76 (524) - 130 (896)
	500 (32)	3560	90 (621) - 127 (876)	90 (621) - 127 (876)	91 (627) - 127 (876)
5×4×11.5 FM	300 (19)	1780	41 (283) - 57 (392)	41 (283) - 57 (392)	41 (283) - 58 (400)
	350 (22)	1780	41 (283) - 57 (393)	41 (283) - 57 (393)	40 (276) - 57 (393)
	400 (25)	1780	40 (276) - 56 (386)	40 (276) - 56 (386)	40 (276) - 57 (393)
	450 (28)	1780	42 (290) - 56 (386)	42 (290) - 56 (386)	41 (283) - 56 (386)
	500 (32)	1780	41 (283) - 55 (379)	41 (283) - 55 (379)	40 (276) - 55 (379)
	500 (32)	3560	158 (1089) - 176 (1213)	158 (1089) - 176 (1213)	158 (1089) - 177 (1220)
	750 (47)	3560	154 (1062) - 171 (1179)	154 (1062) - 171 (1179)	154 (1062) - 172 (1186)
	1000 (63)	3560	145 (1000) - 163 (1124)	145 (1000) - 163 (1124)	146 (1007) - 163 (1124)
8×5×11.5 FM	500 (32)	1780	40 (276) - 52 (359)	40 (276) - 52 (359)	40 (276) - 52 (359)
	750 (47)	1780	41 (283) - 50 (345)	41 (283) - 50 (345)	40 (276) - 50 (345)
6×5×13 FM	400 (25)	1780	45 (310) - 79.5 (548)	45 (310) - 79.5 (548)	45 (310) - 79 (545)
	450 (28)	1780	44.5 (307) - 79 (545)	44.5 (307) - 79 (545)	44 (303) - 79 (548)
	500 (32)	1780	44 (303) - 78.5 (541)	44 (303) - 78.5 (541)	44 (303) - 78 (538)
	750 (47)	1780	41 (283) - 76 (524)	41 (283) - 76 (524)	41 (283) - 76 (524)

TORONTO

23 BERTRAND AVENUE
TORONTO, ONTARIO
CANADA
M1L 2P3
+1 416 755 2291

BUFFALO

93 EAST AVENUE
NORTH TONAWANDA, NEW YORK
U.S.A.
14120-6594
+1 716 693 8813

BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL
HALESOWEN, WEST MIDLANDS
UNITED KINGDOM
B62 8DJ
+44 (0) 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM
M11 2ET
+44 (0) 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN
MARGOSA ROAD, MALLESWARAM
BANGALORE, INDIA
560 003
+91 (0) 80 4906 3555

SHANGHAI

NO. 1619 HU HANG ROAD, XI DU TOWNSHIP
FENG XIAN DISTRICT, SHANGHAI
P.R.C.
201401
+86 21 3756 6696

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO,
1370 GALPÃO 6
EMBU DAS ARTES
SAO PAULO, BRAZIL
+55 11 4781 5500

ARMSTRONG FLUID TECHNOLOGY
ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

SAFETY
HAS A
HOME