

## DESIGN ENVELOPE 4280 END SUCTION | 2x1.5x5 (50-125) | 1505H-003.0 | SUBMITTAL

File No: 103.5715  
Date: MARCH 25, 2021  
Supersedes: 103.5715  
Date: AUGUST 19, 2019

Job: \_\_\_\_\_ Representative: \_\_\_\_\_  
Order No: \_\_\_\_\_ Date: \_\_\_\_\_  
Engineer: \_\_\_\_\_ Submitted by: \_\_\_\_\_ Date: \_\_\_\_\_  
Contractor: \_\_\_\_\_ Approved by: \_\_\_\_\_ Date: \_\_\_\_\_

### PUMP DESIGN DATA

No. of pumps: \_\_\_\_\_ Tag: \_\_\_\_\_  
Capacity: \_\_\_\_\_ USgpm (L/s) Head: \_\_\_\_\_ ft (m)  
Liquid: \_\_\_\_\_ Viscosity: \_\_\_\_\_  
Temperature: \_\_\_\_\_ °F (°C) Specific gravity: \_\_\_\_\_  
Suction: 2" (50 mm) Discharge: 1.5" (40 mm)

**UL STD 778 & CSA STD C22.2 NO.108 certified**

Test report is supplied with each pump

### MATERIALS OF CONSTRUCTION

- ANSI 125**  
CONSTRUCTION: LPDESF  
E-coated ductile iron A536 Gr 65-45-12, stainless fitted
- ANSI 250**  
CONSTRUCTION: HPDESF  
E-coated ductile iron A536 Gr 120-90-2, stainless fitted

### MAXIMUM PUMP OPERATING CONDITIONS

- ANSI 125**  
175 psig at 150°F (12 bar at 65°C)  
100 psig at 300°F (7 bar at 150°C)
- ANSI 250**  
375 psig at 150°F (26 bar at 65°C)  
260 psig at 300°F (21 bar at 150°C)

### MECHANICAL SEAL DESIGN DATA

Seal type: 2A  
Stationary seat: Silicone carbide  
Secondary seal: EPDM  
Spring: Stainless steel  
Rotating hardware: Stainless steel

### DEPM MOTOR AND CONTROL DATA

**HP:** 3  
**RPM:** 3000  
**Motor enclosure:** TEFC  
**Volts:** \_\_\_\_\_  
**Phase:** 3  
**Efficiency:** IE5  
**Protocol (standard):**  BACnet™ MS/TP  BACnet™ TCP/IP  
 Modbus RTU  
**Control enclosure:**  Indoor - UL TYPE 12  
**Fused disconnect switch:** Consult factory  
**EMI/RFI control:** Integrated filter designed to meet EN61800-3  
**Harmonic suppression:** Equivalent: 5% AC line reactor - Supporting IEEE 519-1992 requirements\*\*  
**Cooling:** Fan-cooled, surface cooling  
**Ambient temperature:** -10°C to +45°C up to 1000 meters above sea level (+14°F to +113°F, 3300 ft)  
**Analog I/O:** Two inputs, one output. Output can be configured for voltage or current  
**Digital I/O:** Two inputs, two outputs. Outputs can be configured as inputs  
**Relay outputs:** Two programmable  
**Communication port:** 1-RS485

\*\* If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

### FLOW READOUT ACCURACY

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMS. The model readout will be factory tested to ensure ±5% accuracy.

| FLUID TYPE     | ALL GLYCOLS > 30% WT CONC |                   | ALL OTHER NON-POTABLE FLUIDS |                        | POTABLE (DRINKING) WATER |                   |
|----------------|---------------------------|-------------------|------------------------------|------------------------|--------------------------|-------------------|
| Temperature    | up to 200°F / 93°C        | over 200°F / 93°C | up to 200°F / 93°C           | over 200°F / 93°C      | up to 200°F / 93°C       | over 200°F / 93°C |
| Rotating face  | Silicone carbide          |                   | Resin bonded carbon          | Antimony loaded carbon | Resin bonded carbon      |                   |
| Seat elastomer | EPDM (L-cup)              | EPDM (O-ring)     | EPDM (L-cup)                 | EPDM (O-ring)          | EPDM (L-cup)             | EPDM (O-ring)     |
| Material code  | SCsc L EPSS 2A            | SCsc O EPSS 2A    | C-sc L EPSS 2A               | ACsc O EPSS 2A         | C-sc L EPSS 2A           | C-sc O EPSS 2A    |

## OPTIONS

### SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained \_\_\_\_\_ ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

### PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained \_\_\_\_\_ ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

### ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- **Auto-flow balancing** - Automatically determines control curve between design flow at on-site system head, and minimum (zero-head) flow for energy savings
- **Maximum flow control** - Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate \_\_\_\_\_ gpm (L/s)

\*Only available if sensorless bundle is enabled

\*Available in single pump operation only

### PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- **Minimum flow control** - Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- **Bypass valve control** - Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate \_\_\_\_\_ gpm (L/s)

\*Only available if sensorless bundle is enabled

### DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

#### Cooling

Duty point \_\_\_\_\_ gpm (L/s) at \_\_\_\_\_ ft (m)

Minimum system pressure to be maintained \_\_\_\_\_ ft (m)

#### Heating

Duty point \_\_\_\_\_ gpm (L/s) at \_\_\_\_\_ ft (m)

Minimum system pressure to be maintained \_\_\_\_\_ ft (m)

\*Available in single pump operation only

## OPTIONAL SERVICES

### ON-SITE PUMP COMMISSIONING



### PUMP MANAGER




Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

\* Requires an internet connection to be provided by building


\* Includes an extended warranty for parts and labour (wearable parts excluded)

3




Performance curves are for reference only.  
Confirm current performance data with Armstrong ADEPT Quote or ADEPT Select selection software.

**STANDARD**



**SEISMIC MOUNT OPTION**



**NOTE:**  
All springs have additional travel to solid equal to 50% of the rated deflection.

**DIMENSION DATA**

**STANDARD**

|                                     |             |
|-------------------------------------|-------------|
| <b>Size:</b>                        | 2×1.5×5     |
| <b>HP:</b>                          | 3           |
| <b>RPM:</b>                         | 3000        |
| <b>HA:</b>                          | 10.32 (262) |
| <b>HD:</b>                          | 8.75 (222)  |
| <b>HI:</b>                          | 18.27 (464) |
| <b>HV:</b>                          | 8.18 (208)  |
| <b>X:</b>                           | 7.00 (178)  |
| <b>Y:</b>                           | 4.00 (102)  |
| <b>Free &amp; operating height:</b> | 3.75 (95)   |
| <b>Weight:</b>                      | 84 (38.0)   |

**SPRING DATA**

|   |           |
|---|-----------|
| <b>Rated Capacity per spring lbs (kgs):</b> | 54 (25.0) |
| <b>Rated Deflection inch (mm):</b>          | 1.20 (30) |
| <b>Mount Constant lbs/in (kg/mm):</b>       | 45 (0.8)  |



**SEISMIC MOUNT OPTION**

|   |             |
|---|-------------|
| <b>ZE:</b>                              | 5.75 (146)  |
| <b>F:</b>                               | 4.00 (102)  |
| <b>G:</b>                               | 6.00 (152)  |
| <b>H:</b>                               | 0.50 (12)   |
| <b>HA:</b>                              | 10.32 (262) |
| <b>HD:</b>                              | 10.00 (254) |
| <b>N:</b>                               | 6.52 (166)  |
| <b>Free &amp; operating height:</b>     | 5.00 (127)  |
| <b>Max. horizontal static G rating:</b> | 6.7         |



Dimensions - inch (mm)  
Weight - lbs (kg)

- Tolerance of ±0.125" (±3 mm) should be used
- For exact installation, data please write factory for certified dimensions

STANDARD



SEISMIC MOUNT OPTION



TORONTO  
+1 416 755 2291

BUFFALO  
+1 716 693 8813

BIRMINGHAM  
+44 (0) 8444 145 145

MANCHESTER  
+44 (0) 8444 145 145


BANGALORE  
+91 (0) 80 4906 3555

SHANGHAI  
+86 (0) 21 5237 0909

SÃO PAULO  
+55 11 4785 1330

LYON  
+33 (0) 420 102 625

DUBAI  
+971 4 887 6775



MANNHEIM  
+49 (0) 621 3999 9858