

DESIGN ENVELOPE 4280 END SUCTION |

1506-007.5 | SUBMITTAL

File No: 100.3512
Date: APRIL 18, 2016
Supersedes: NEW
Date: NEW

Job: _____ Representative: _____
 _____ Order No: _____ Date: _____
 Engineer: _____ Submitted by: _____ Date: _____
 Contractor: _____ Approved by: _____ Date: _____

PUMP DESIGN DATA

No. of pumps: _____ Tag: _____
 Capacity: _____ USgpm (L/s) Head: _____ ft (m)
 Liquid: _____ Viscosity: _____
 Temperature: _____ °F (°C) Specific gravity: _____
 Suction: 3" (75mm) Flanged
 Discharge: 1.5" (40mm) Flanged
OSHDP Seismic Certification osp-0422-10
UL STD 778 & CSA STD C22.2 NO.108 certified

MOTOR DESIGN DATA

HP: 7.5 RPM: 3600 Frame size: 213JM
 Enclosure: TEFC Volts: _____ Hertz: 60 Hz
 Phase: 3 Efficiency: NEMA premium 12.12

MAXIMUM PUMP OPERATING CONDITIONS

ANSI 125

175 psig at 150°F (12 bars at 65°C)
 140 psig at 250°F (10 bars at 121°C)

ANSI 250

300 psig at 150°F (20 bars at 65°C)
 250 psig at 250°F (17 bars at 121°C)

- Tolerance of ±0.125" (±3 mm) should be used
- For exact installation, data please write factory for certified dimensions

MECHANICAL SEAL DATA

Seal type: 2A **Stationary seat:** Silicone carbide
Secondary seal: EPDM **Rotating hardware:** Stainless steel
Spring: Stainless steel


CONTROLS DATA

Sensorless control: Standard
Minimum system pressure to be maintained: _____ ft (m)*
Protocol (standard): Modbus RTU BACnet™ MS/TP
 Johnson® N2 Siemens® FLN
Protocol (optional): LonWorks®
Enclosure: Indoor - UL TYPE 12
Fused disconnect switch:
EMI/RFI control: Integrated filter designed to meet EN61800-3
Harmonic suppression: Dual dc-link reactors (equivalent: 5% AC line reactor) supporting IEEE 519-1992 requirements**
Cooling: Fan-cooled through back channel
Ambient temperature: -10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
Analog I/O: Two current or voltage inputs, one current output
Digital I/O: Six programmable inputs (two can be configured as outputs)
Pulse inputs: Two programmable
Relay outputs: Two programmable
Communication port: 1-RS485, 1-USB

*If minimum maintained system pressure is not known: Default to 40% of design head
 **The Ivs 102 drive is a low harmonic drive via built-in dc line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

| FLUID TYPE | ALL GLYCOLS > 30% WT CONC | | ALL OTHER NON-POTABLE FLUIDS | | POTABLE (DRINKING) WATER | |
|-----------------------|---------------------------|-------------------|------------------------------|------------------------|--------------------------|-------------------|
| | up to 200°F / 93°C | over 200°F / 93°C | up to 200°F / 93°C | over 200°F / 93°C | up to 200°F / 93°C | over 200°F / 93°C |
| Temperature | up to 200°F / 93°C | over 200°F / 93°C | up to 200°F / 93°C | over 200°F / 93°C | up to 200°F / 93°C | over 200°F / 93°C |
| Rotating face | Silicone carbide | | Resin bonded carbon | Antimony loaded carbon | Resin bonded carbon | |
| Seat elastomer | EPDM (L-cup) | EPDM (O-ring) | EPDM (L-cup) | EPDM (O-ring) | EPDM (L-cup) | EPDM (O-ring) |
| Material code | SCSc L EPSS 2A | SCSc O EPSS 2A | C-SC L EPSS 2A | ACSc O EPSS 2A | C-SC L EPSS 2A | C-SC O EPSS 2A |

EXTENDED SPEED



Performance curves are for reference only.
Confirm current performance data with Armstrong ACE Online selection software.

DIMENSION DATA

| INDOOR (UL TYPE 12/ODP) | |
|----------------------------|-------------|
| Frame size: | 213JM |
| Size: | 3×1.5×6 |
| HP: | 7.5 |
| RPM: | 3600 |
| A: | 10.27 (261) |
| B: | 7.48 (190) |
| C MAX: | 22.30 (566) |
| D1: | 5.25 (133) |
| D2: | 5.25 (133) |
| 2E: | 8.50 (216) |
| F: | 5.50 (140) |
| H: | 0.47 (12) |
| HD: | 7.68 (195) |
| HI: | 21.91 (556) |
| HV: | 14.42 (366) |
| N: | 7.24 (184) |
| NAN1: | 6.00 (152) |
| X: | 6.50 (165) |
| Y: | 4.00 (102) |
| Casing foot hole: | 0.63 (16) |
| Weight: | 284 (128.8) |

Dimensions - inch (mm)
Weight - lbs (kg)

INDOOR

- TORONTO
+1 416 755 2291
- BUFFALO
+1 716 693 8813
- BIRMINGHAM
+44 (0) 8444 145 145
- MANCHESTER
+44 (0) 8444 145 145
- BANGALORE
+91 (0) 80 4906 3555
- SHANGHAI
+86 21 3756 6696
- SÃO PAULO
+55 11 4781 5500

